





- NOTE:
1. ELECTRICAL CHARACTERISTIC:
    - 1) VOLTAGE CURRENT RATING: 0.5AMP, 100V AC
    - 2) INSULATION RESISTANCE: 100MΩ MIN;
    - 3) CONTACT RESISTANCE: 30mΩ MAX;
    - 4) DIELECTRIC WITHSTANDING VOLTAGE: AC 500V R.M.S.
  2. Mechanical:
    - 1) Mating Force: 35 N MAX
    - 2) Unmating Force: 10 N MIN.
  3. DIMENSIONS MARKED '▼' TO BE CHECKED BY Q.C & IPQC.

| Bill of materials: |          |                      |     |                                      |            |         |
|--------------------|----------|----------------------|-----|--------------------------------------|------------|---------|
| 3                  | HOUSING  | PA9T+30%GF, UL94 V-0 | 1   | UL 94V-0                             | X. ±0.3    | X.' ±2" |
|                    |          |                      |     |                                      | .X ±0.2    | .X" ±1" |
| 2                  | SHELL    | SPCC/STEEL           | 1   | PLATED Ni                            | .XX ±0.15  | .XX"    |
|                    |          |                      |     |                                      | .XXX ±0.10 | .XXX"   |
| 1                  | TERMINAL | COPPER ALLOY (C2680) | 4   | Gold flash on contact<br>tin on tail |            |         |
| NO                 | PARTS    | MATERIAL             | QTY | FINISHING                            |            |         |