

**G 20/0.63A/F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

For protection against overcurrent, we offer cartridge fuse with dimensions 5x20 mm in sizes from 100 mA to 6.3 A.

**General ordering data**

| Version    | Active components, Fuse    |
|------------|----------------------------|
| Order No.  | <a href="#">0439000000</a> |
| Type       | G 20/0.63A/F               |
| GTIN (EAN) | 4008190131210              |
| Qty.       | 10 pc(s).                  |

**G 20/0.63A/F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Depth      | 5 mm  | Depth (inches)  | 0.197 inch |
| Height     | 20 mm | Height (inches) | 0.787 inch |
| Width      | 5 mm  | Width (inches)  | 0.197 inch |
| Net weight | 1.1 g |                 |            |

**Environmental Product Compliance**

|            |                |      |                                      |
|------------|----------------|------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 | SCIP | e55693ba-5f1b-4f6e-b99e-8d57d3de2235 |
|------------|----------------|------|--------------------------------------|

**Material data**

|        |            |
|--------|------------|
| Colour | Light Grey |
|--------|------------|

**System specifications**

|         |                  |
|---------|------------------|
| Version | Fuse accessories |
|---------|------------------|

**Fuse cartridges**

|                         |                       |                          |              |
|-------------------------|-----------------------|--------------------------|--------------|
| Cartridge fuse          | G-Si. 5 x 20          | Characteristics          | quick-acting |
| Colour                  | Light Grey            | Current                  | 0.63 A       |
| Melting integral        | 0.31 A <sup>2</sup> s | Optical function display | No           |
| Power output (@ 1.5 In) | 1.1 W                 | Rated breaking capacity  | 1.5 kA       |
| Version                 | Fuse accessories      | Voltage drop             | 550 mV       |

**Rating data**

|               |          |               |        |
|---------------|----------|---------------|--------|
| Rated voltage | 250 V AC | Rated current | 0.63 A |
|---------------|----------|---------------|--------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000035    | ETIM 7.0    | EC000035    |
| ETIM 8.0    | EC002704    | ECLASS 9.0  | 27-14-20-01 |
| ECLASS 9.1  | 27-14-20-01 | ECLASS 10.0 | 27-14-20-01 |
| ECLASS 11.0 | 27-14-20-01 | ECLASS 12.0 | 27-14-20-01 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |                                                 |
|--------------------|-------------------------------------------------|
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |                                                 |