

1000 Series SMB

50 Ohm Cable and PCB Connectors



Bomar products, like the 1000 Series 50 Ohm SMB Connectors, are now sold under the Win™ brand from Winchester Interconnect™.

Product Description

Winchester Interconnect's 1000 Series 50 Ohm SMB Connectors can be used in a wide range of applications including Test and Measurement, Mil-Aero, Satellite Communication, Wireless Communication, and Medical Equipment.

Our 1000 Series SMB Connectors are designed in accordance with MIL-STD 348 and feature a "Snap-On" interface designed for a frequency range of DC to 4 GHz.

Male cable plug connectors are available in straight and right-angle designs for popular flexible and semi-rigid cables.

Printed circuit board (PCB) connectors are available in straight and right-angle through-hole solder, and also in our unique E-Snap® Edge-Mount design.



- Quick connect disconnect snap-on mating reduces installation time.



- Jack connectors have a male center contact. Plug connectors have a female center contact.



- SMB connectors are 30% smaller than SMA connectors.

Specifications

Electrical Impedance 50 Ohms	Contact Resistance Center ≤ 6 Megohms Outer ≤ 1 Megohms	Disengagement Force ≥ 1.8 lbs.	Insulator PTFE	Corrosion MIL-STD-202, Method 101
Frequency DC to 4 GHz	Insulation Resistance 5000 Megohms Min	Connector Durability 500 Cycles Min	Crimp Ferrule Copper/Brass Nickel/ Gold Plated	Mechanical Shock MIL-STD-202, Method 101
Working Voltage ≥ 250 VRMS	Mechanical Contact Retention ≥ 4 lbs.	Material Body & Outer Contact Brass Nickel or Gold Plated	Environmental Temperature Range -55°C to +155°C	Humidity MIL-STD-202, Method 101
Dielectric Withstanding Voltage 1000 VRMS at sea level	Engagement Force ≤ 17 lbs.	Male Contact Brass Gold Plated	Thermal Shock MIL-STD-202, Method 107	
VSWR Straight 1.3 Max Right-Angle 1.5 Max		Female Contact BECU Gold Plated	Moisture Resistance MIL-STS-202, Method 105	

Part Numbers

Part Number	Straight and Right-Angle Cable Plugs	Crimp Tool	Hex Size
1010A204F	Straight Cable Plug for RG178, RG196	BDHD200	Solder / 0.128
1010A204M	Straight Cable Plug for RG174, RG316, LMR100	BDHD200	Solder / 0.128
1010A204MS	Straight Cable Plug for RD316	BDHD200	Solder / 0.151
1013A204F	Right-Angle Cable Plug for RG178, RG196	BDHD200	Solder / 0.128
1013A204M	Right-Angle Cable Plug for RG174, RG316, LMR100	BDHD200	Solder / 0.128
1013A204MS	Right-Angle Cable Plug for RD316	BDHD200	Solder / 0.151

Part Number	Bulkhead Cable Jacks	Crimp Tool	Hex Size
1021A204M	Straight Bulkhead Jack for RG174, RG316, LMR100	BDHD200	Solder / 0.128
1021A204MS	Straight Bulkhead Jack for RD316	BDHD200	Solder / 0.151

Part Number	Printed Circuit Board Connectors	PCB Thickness	Packaging
1061A514	Vertical, SMB, Jack, 0.155" Solder Tail	0.062"	Single Pack
1064A595	Right-Angle, SMB, Jack, 0.155" Solder Tail	0.062"	Single Pack
1063A595	Right-Angle, SMB, Plug, 0.155" Solder Tail	0.062"	Single Pack
1060A514	Vertical, SMB, Plug, 0.155" Solder Tail	0.062"	Single Pack

Part Number	2- and 4- Hole Flange Solder Cup	Mounting
1017A524	Square Flange Jack Solder Cup	4-Hole Pattern
1017B524	Rectangular Flange Jack Solder Cup	2-Hole Pattern

Win Bomar products are now under the Win™ brand from Winchester Interconnect.