



LOC		DIST		REV		REVISIONS		DATE	APPD
G	14	P	F	ZONE	LTR	DESCRIPTION		2-16-93	18 DAP
				0		RELEASED PER 0720-0008-93			



AMP WIRE RANGE	UL E13288 Listed
26-22 AWG STRANDED	NOT LISTED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES		DR 2-16-93 TA BRINKMAN	AMP AMP Incorporated Harrisburg, PA 17105-3608
MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 2-16-93 DA PATTERSON	
FINISH TIN PLATE 0.00254 [L.000100] MIN THK PER MIL-T-10727		APPD 2-16-93 JL MECKLEY	
APPLICATION SPEC		NAME	TERMINAL, SPADE TONGUE, BUDGET
WEIGHT		SIZE	CAGE CODE
-		G	00779
SCALE 10:1		DRAWING NO	G-32501
		SHEET	1 OF 1

32501
PART NO