




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
03 ₁	ECN 94-0474	1/31/95	<i>RR</i>

NOTE: CAPTURED CENTER CONTACT

HOUSING CAP	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35			
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A			
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204			
COMPONENT	MATERIAL	FINISH			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	DRAWN BY RR 5/12/80	AMP AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599			
	CHECKED BY K DALY 5/15/80				
	APPD BY GH 5/23/80				
These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE	TITLE OSSM 4 HOLE FLANGE MOUNT RIGHT ANGLE JACK RECEPTACLE - SOLDER POT TERMINAL			
	NO. AP. N/A	SIZE B	CODE IDENT NO. 26805	1054-5005-02	REV 03 ₁
		SCALE 4:1			
					SHEET 1 OF 1

CUSTOMER DRAWING

AMP PART # 1045621-1
SHEET 1 OF 1 REV A