




- NOTES:
- 1. MATERIALS AND FINISHES:
 - BODY & C NUT - BERYLLIUM COPPER, GOLD PLATING
 - CONTACT - BERYLLIUM COPPER, GOLD PLATING
 - INSULATOR - PTFE
 - 2. ELECTRICAL:
 - A. IMPEDANCE: 50 OHM
 - B. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
 - 3. MECHANICAL:
 - A. DURABILITY: 500 CYCLES MIN.
 - B. TEMPERATURE RANGE: -65° C TO +165° C
 - 4. PACKAGING:
 - A. QUANTITY: SINGLE PACK
 - B. MARKING: BAG TO BE MARKED
 - "AMPHENOL, 901-101-15, AND DATE CODE"
 - 5. SHOWS CABLE ENTRY DIMENSION



RECOMMENDED CABLE STRIPPING DIMENSION

901-101-15		REVISIONS			
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	--	RELEASE TO MFG.	--	--	--
	W	REDRAWN IN PRO-E, ADDED SHT 2	8/10/09	47526	NMV



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1°	MATERIAL	DRAWN NISCHIT MV	DATE 12-Jun-09	TITLE SMA CONNECTOR CRIMP TYPE PLUG FOR RG400/U & RG 142B/U CABLE		Amphenol RF Danbury, CT, USA Tainan, Taiwan Shenzhen, China www.amphenolrf.com	
		ENGINEER RPA	DATE 6/29/71				
	REFERENCE	APPROVED K. CAPOZZI	DATE 8/10/09	SCALE: 8.0:1		SHEET 2 OF 2	
		CAD FILE I:SMA/ 901-101-15		CODE ID 74868	DWG SIZE B	DRAWING NO. 901-101-15	REV W