




REV. 0

DCO 143174


COIL: @ 25°C
 RESISTANCE 6500 OHMS ±10%
 NOMINAL VOLTAGE 36.0 VDC
 MUST OPERATE 20.0 VDC
 MUST RELEASE 10.0 VDC MAX, 1.8 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX.
 RELEASE TIME 2.0 MS MAX.
 CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 8/24/01

OK JEP 8/24/01

CII Technologies
 advanced control electronic solutions

CUST. QPL
 CUST. NO. M39016/11-037P REV.

"JMS"RELAY

JMSC-36XP