




ISOMETRIC



RECOMMENDED PCB LAYOUT



▲ SCHEMATIC

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT RATING: 50mA @ 12VDC
5. TRAVEL: 0.25 +0.2/-0.1mm
6. CONTACT RESISTANCE: 100 Milli-Ohms Max.
7. OPERATING FORCE: 160 ± 50gf
- ▲ 8. CONTACT MATERIAL: GOLD
9. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 10. PACKAGE: TRAY/ 200 PIECES PER
11. 2002/95/EC (ROHS) COMPLIANT



C	19576	DRAWING UPDATES / CLEAN-UP	1/11/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
TITLE			TL53CF160R (GOLD CONTACTS)	
SCALE	2:1	DATE	1/11/2011	DR BGL
			DWG	P010612
			REV	C