

**OVERVIEW**

**PRODUCT IMAGE**  
COMING SOON

**DESCRIPTION**

Board to Board connector, Unshrouded Header, Through Hole, Single Row, 2 Position, Vertical.

**DOCUMENTATION**

Product Drawing

**PRODUCT ENVIRONMENTAL COMPLIANCE**

Click to download [Certificate of Compliance Report](#)

EU RoHS: [Compliant](#)

China RoHS: [Compliant](#)

Low Halogen: [No](#)

REACH/SVHC: [Compliant](#)
**DISTRIBUTOR STOCK CHECK**
[AMERICAS](#)
[EUROPE](#)
[ASIA](#)

Distributor Name	Stock	Updated Date	
Digi-Key Electronics	511	12/20/2020	<a href="#">Buy Now</a>

**PART SPECIFICATION DETAIL**

The information below is for reference only. For more technical details, refer to product specification and application specification.

Number of Contacts	2	Number of Rows	1
Orientation	Straight	Termination Style	DIP
Length (Overall pin)	12.60mm (0.496in)	Mating Length	7.00mm (0.275in)
Pitch	2.54mm (0.100in)	Tail Length	3.00mm (0.118in)
Current Rating	3A Continuous	Resistance (Insulation)	1000MΩ
Voltage Rating	1000V AC rms	Color - Housing	Black
Flammability Rating	UL 94 V-0	Material Contact	Copper Alloy
Material Housing	Self Extinguishing Thermoplastic	Operating Temperature Range	-55°C to +125°C
Plating Contact area	Gold Flash	Tail Plating	Gold Flash
Retention Feature	No	Packaging	Bulk Packaging

**AMPHENOL ICC**
[ABOUT US](#)  
[CAREERS](#)  
[SITEMAP](#)
**SUPPORT**
[CONTACT US](#)  
[LIVE CHAT](#)  
[DISTRIBUTOR](#)  
[AMPHENOL ICC SALES OFFICES](#)
**FOLLOW US**

**NEWSLETTER**
 Enter your email address: [SUBMIT](#)

Signing up for newsletter indicates you agree with our [Terms of Services](#).

