





| REAL CODE |   |   |   |   |   |
|-----------|---|---|---|---|---|
|           | C | 1 | 2 | 4 | 8 |
| 0         | ● |   |   |   | 0 |
| 1         | ● | ● |   |   | 1 |
| 2         | ● |   | ● |   | 2 |
| 3         | ● |   |   |   | 3 |
| 4         | ● |   |   | ● | 4 |
| 5         | ● |   |   | ● | 5 |
| 6         | ● |   | ● |   | 6 |
| 7         | ● | ● | ● |   | 7 |
| 8         | ● |   |   |   | 8 |
| 9         | ● | ● |   |   | 9 |
| 10        | ● |   | ● |   | A |
| 11        | ● | ● |   |   | B |
| 12        | ● |   | ● | ● | C |
| 13        | ● | ● |   | ● | D |
| 14        | ● |   | ● | ● | E |
| 15        | ● | ● | ● | ● | F |



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4  
X.XX=± 0.25
3. TERMINAL NUMBERS FOR REFERENCE ONLY
4. OPERATING FORCE: 120gf/cm ± 30gf
- ▲ 5. CONTACT RATING: 100mA, 42V DC (SWITCHING)  
400mA 42V DC (NON-SWITCHING)
6. CONTACT RESISTANCE: 80mΩ MAX.
7. INSULATION RESISTANCE: 100MΩ MIN @ 250VDC
8. DIELECTRIC STRENGTH: 250VAC 1 MIN.
9. LIFE: 25,000 STEPS
10. OPERATING TEMPERATURE: -60°C TO 125°C
11. PACKAGING: 65 PCS TUBE
12. IP RATING: IP67
13. ▲ DENOTES CRITICAL PARAMETER
14. 2002/95/EC (ROHS) COMPLIANT



TITLE RDMA16R2T

|     |        |             |         |     |
|-----|--------|-------------|---------|-----|
| A   | 21365  | NEW RELEASE | 1/31/14 | EBP |
| REV | PCR NO | DESCRIPTION | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|       |                   |           |                |          |
|-------|-------------------|-----------|----------------|----------|
| SCALE | DATE<br>1/31/2014 | DR<br>EBP | DWG<br>U100015 | REV<br>A |
|-------|-------------------|-----------|----------------|----------|