


- ⚠

MATERIAL: POLYPHENYLENE OXIDE MOLDING COMPOUND. SEE TABLE FOR COLOR.
2. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. 100 KITS BULK PACKAGED.



SUPERSEDED BY 4-552008-1	12.19-13.97[.480-.550]	ALMOND	4-552007-2	4-552006-2	4-552008-2
	12.19-13.97[.480-.550]	BLACK	4-552007-1	4-552006-1	4-552008-1
	8.38-9.65[.330-.380]	BLACK	3-552007-1	3-552006-1	3-552008-1
	9.65-10.92[.380-.430]	BLACK	2-552007-1	2-552006-1	2-552008-1
	10.92-12.45[.430-.490]	GRAY	552007-4	552006-4	552008-4
	10.92-12.45[.430-.490]	BLACK	552007-1	552006-1	552008-1
CABLE RANGE DIAMETER		COLOR	GROOVE SIDE PART NO.	TONGUE SIDE PART NO.	KIT PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

⚠

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

FINISH

-

DWN
D. STRAUSSER
16APR97

CHK
M. HUGHES
21APR97

APVD
M. HUGHES
21APR97

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

COVER KIT, 180 DEGREE,
50 POSITION, CHAMP

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=552008

RESTRICTED TO

-

SCALE

2:1

SHEET

1 of 1

REV

U2