




NOTES:

1. MATERIAL:


- 1.1 HOUSING: HIGH TEMPERATURE THERMO PLASTIC,UL94V-0,COLOR:BLACK.
- 1.2 CONTACT: COPPER ALLOY.
- 1.3 SOLDER PEG AND LATCH:STAINLESS STEEL.

2. FINISH:

SOLDER PEG: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
CONTACT SOLDER AREA: GOLD FLASH ON SOLDERTAIL.

- 2.1 CONTACT AREA: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.2 CONTACT AREA: 5u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.3 CONTACT AREA: 10u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.4 CONTACT AREA: 15u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.5 CONTACT AREA: 30u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.

3. COPLANARITY: 0.10 MAX. (BEFORE SOLDERING)




MATING: ① INSERTING(25°) → ② ROTATING → ③ FIXED

UNMATING: ④ UNFIXED → ⑤ ROTATING → ⑥ WITHDRAWING

TAPE&REEL	BLACK	1.2V	30u"	260	2309408-5
TAPE&REEL	BLACK	1.2V	15u"	260	2309408-4
TAPE&REEL	BLACK	1.2V	10u"	260	2309408-3
TAPE&REEL	BLACK	1.2V	5u"	260	2309408-2
TAPE&REEL	BLACK	1.2V	GF	260	2309408-1
PACKING TYPE	HOUSING COLOR	POWER SUPPLY	FINISH	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016	TE Connectivity		
		CHK RICHARD MA 09SEP2016			
		APVD SIMON LI 09SEP2016	NAME		
		PRODUCT SPEC	DDR4 SODIMM SOCKET		
		108-115122	0.5mm PITCH 260POS		
		APPLICATION SPEC	4.0mm HEIGHT REVERSE TYPE		
		—	SIZE	CAGE CODE	DRAWING NO
		WEIGHT	A2	00779	2309408
		CUSTOMER DRAWING	SCALE	1:1	SHEET 1 OF 3
					REV 4



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	—	—	—	—

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016	TE Connectivity		
		CHK RICHARD MA 09SEP2016			
DIMENSIONS: mm		APVD SIMON LI 09SEP2016	NAME		
		PRODUCT SPEC	DDR4 SODIMM SOCKET		
		APPLICATION SPEC	0.5mm PITCH 260POS		
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO
		FINISH	A2	00779	C=2309408
		ANGLES	RESTRICTED TO		
CUSTOMER DRAWING			SCALE	SHEET	REV
			—	3 of 3	4