





▲ SPDT ON-(ON)
CONTACT CONFIGURATION
() DENOTES MOMENTARY
FUNCTION

F.P. (MM)	O.P. (MM)	M.T. (MM)
11.4 ± 0.5	9.6 ± 0.8	2.3

F.P. = FREE POSITION
O.P. = OPERATING POSITION
M.T. = MAX TRAVEL POSITION


NOTES:

- ALL DIMENSIONS IN MM
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REFERENCE ONLY
- ELECTRICAL LIFE: 6,000 CYCLES
- OPERATING TEMP: 0°C TO 85°C
- CONTACT RESISTANCE: 30mΩ MAX. INITIAL
- 2011/65/EU (ROHS) COMPLIANT
- ▲ DENOTES CRITICAL PARAMETER
- CONTACT RATING: UL 16A 125VAC, 12A 250VAC, 1HP 125/250VAC



▲ WHITE
ACTUATOR

▲ WHITE
HOUSING



E-SWITCH®

B	22570	ADDED PIN NUMBERS	10/28/16	MJR
A	22496	NEW RELEASE	9/13/16	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PP1-4B7-2D2

SCALE 1:1

DATE 9/13/2016

DR MJR

DWG 34-PP14B72D2

REV B