





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	06FEB2021	SR	AP




PTFE INSULATED CABLE



3:10
ISO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

- 0 PLC ±
- 1 PLC ±
- 2 PLC ±
- 3 PLC ±
- 4 PLC ±
- ANGLES ±

MATERIAL

-

FINISH

-

DWN SUPREETH R 06FEB2021

CHK A. PILE 06FEB2021

APVD A. PILE 06FEB2021

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME Aluminium Housed Breaking Resistor
Type HCH335

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-2176466

RESTRICTED TO

-

SCALE

1:2

SHEET

1 OF 2

REV


A

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SCHEDULE

TCPN	PRODUCT NUMBER	MATERIAL DESCRIPTION	LEAD LENGTH
2176466-1	HCH335J10RJ	HCH335 500W 10R 5% LEAD	300mm
2176466-2	HCH335J22RJ	HCH335 500W 22R 5% LEAD	300mm
2176466-3	HCH335J33RJ	HCH335 500W 33R 5% LEAD	300mm
2176466-4	HCH335J47RJ	HCH335 500W 47R 5% LEAD	300mm
2176466-5	HCH335J68RJ	HCH335 500W 68R 5% LEAD	300mm
2176466-6	HCH335J82RJ	HCH335 500W 82R 5% LEAD	300mm
2176466-7	HCH335J100RJ	HCH335 500W 100R 5% LEAD	300mm
2176466-8	HCH335J220RJ	HCH335 500W 220R 5% LEAD	300mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUPREETH R 06FEB2021	 TE Connectivity	
		CHK A. PILE 06FEB2021		
DIMENSIONS: mm		APVD A. PILE 06FEB2021	NAME Aluminium Housed Breaking Resistor Type HCH335	
		PRODUCT SPEC -	-	
		APPLICATION SPEC -	-	
MATERIAL -		WEIGHT -	SIZE A3	CAGE CODE 00779
			DRAWING NO C-2176466	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 1:1
		SHEET 2 OF 2		REV A