




DESIGNED FOR USE WITH .141 S.R. CABLE ENTRY DIAMETER MINIMUM	REVISIONS			
	REV	DESCRIPTION	DATE	APPROVED
HOUSING	02	1	REVISED	ADP 5/27/96
BUSHING				

BEFORE CRIMPING	.502 REF 12.8	.385 REF 9.8
AFTER CRIMPING	.392 MAX 10.0	.270 REF 6.9
	DIM 'A'	DIM 'B'

HOUSING COUPLING NUT BUSHING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ± .005 ± 1°	DRAWN BY R.GIERAS 3/21/85 CHECKED BY R.GIERAS 3/21/85 APPD BY R.GIERAS 3/21/85	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599
These drawings and specifications are the property of M/A-COM Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE 408-04664 (20-572) NO. AP.	TITLE 'OSM' STRAIGHT CABLE PLUG SOLDERLESS COMPRESSION CRIMP ATTACHMENT M39012/92B3101
	SIZE B	CODE IDENT NO. 26805
	SCALE 6:1	2001-8931-92
		REV 02
		SHEET 1 OF 1

NOTES:

1. DESIGNED FOR USE WITH .141 DIA (RG 402/U) SEMI-RIGID CABLE
2. PICTORIAL VIEW IS AFTER CRIMPING
3. MIN STRAIGHT CABLE LENGTH: .287
4. IT IS SUGGESTED TO BEND CABLE PRIOR TO CRIMPING

.XXX = in
XX.X = mm (REF)

CUSTOMER DRAWING

AMP PART # 1050809-1
SHEET 1 OF 1 REV A