


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/05/08	D.N.



NOTES:

MATERIALS:

1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
2. CONTACT & FERRULE = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
3. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
4. GASKET = SILICONE RUBBER 45-55 DUROMETER DOW CORNING SILASTIC 250.
5. "O" RINGS = SILICONE RUBBER PER ZZ-R-765, CLASS 2B, GRADE 65-75.
6. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

1. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.
2. ALL OTHER METAL PARTS= NICKEL PLATE PER QQ-N-290, CLASS 1, GRADE G, EXCEPT .0001 TO.0002 THICK OVER .00005 TO .0001 THICK COPPER PER MIL-C-14550.

Property of Radiall Incorporated
This document cannot be reproduced or
communicated to a third party without prior
written permission of RADIALL Incorporated.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: D.N.	DATE 12/05/08	 APPLIED ENGINEERING PRODUCTS 104 John W. Murphy Dr. New Haven, CT 06513				
		CHKD: A.D.M.	DATE 12/05/08					
DECIMAL	ANGLE	APVD: J.M.	DATE 12/05/08	TNC STRAIGHT JACK BULKHEAD FRONT MOUNT WATERTIGHT COMPRESSION TYPE FOR RG-58 & SIMILIAR CABLES				
REFERENCE: ORIGINATOR: D.N. DATE: 12/05/08		MATERIALS AND FINISHES: SEE NOTES		SIZE A	FSCM NO. 19505	DWG NO. 6002-7551-106	REV A	
				SCALE 4:1		THIRD ANGLE PROJECTION		SHEET 1 OF 1

6002-7551-106