

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .

© COPYRIGHT 2011 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B4	REVISED (ECO-14-012616), OBSOLETE 3-6.	30DEC2014	LL	SH




LED SCHEMATIC	
POSITION 2	POSITION 1
GREEN	YELLOW
9+  -10	11+  -12
FOR 1734320-X	



DETAIL B(SCEALE 2:1)

LED SCHEMATIC	
POSITION 2	POSITION 1
YELLOW	GREEN
9+  -10	11+  -12
FOR 1-1734320-X	

LED SCHEMATIC	
POSITION 2	POSITION 1
GREEN	GREEN
9+  -10	11+  -12
	YELLOW
FOR 4-1734320-X	



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05 (TOP VIEW)

NOTE:

- MATERIAL:
HOUSING: PA46, WITH 30% GF.
UL 94V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
SHELL: BRASS.
LED SOLDER TAIL: STEEL.
- FINISH:
CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA,
GOLD PLATED ON SOLDER TAIL,
WITH ENTIRE CONTACT UNDERPLATED
1.27μm [50μ"] MIN. NICKEL.
SHELL: 0.508μm [20μ"] MIN. NICKEL PLATED.
LED SOLDER TAIL: 2.159μm [85μ"] MIN. TIN PLATED.
- RECOMMENDED PCB THICKNESS: 1.6mm.
- WAVE SOLDER CAPABLE TO 265°C PER TE SPEC 109-202, CONDITION B.
- OBsolete PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5 OBSOLETE	GREEN	GREEN/ YELLOW	1.27μm [50μ"]	4=1734320=4
			0.762μm [30μ"]	4=1734320=3
			0.381μm [15μ"]	4=1734320=2
			0.152μm [6μ"]	4=1734320=1
5 OBSOLETE	YELLOW	GREEN	1.27μm [50μ"]	1=1734320=4
			0.762μm [30μ"]	1=1734320=3
			0.381μm [15μ"]	1=1734320=2
			0.152μm [6μ"]	1=1734320=1
	GREEN	YELLOW	1.27μm [50μ"]	1734320=4
			0.762μm [30μ"]	1734320=3
			0.381μm [15μ"]	1734320=2
			0.152μm [6μ"]	1734320=1
	POSITION 2	POSITION 1	MIN. GOLD THICKNESS	PART NUMBER
	INDICATOR COLOR			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HSING 09JUN2009	 TE Connectivity	
		CHK S. CHIEN 09JUN2009		
		APVD W. KODAMA 09JUN2009	NAME	
DIMENSIONS: mm		PRODUCT SPEC 108-57535	MODULAR JACK CONNECTOR RJ45, SINGLE PORT, SIDE ENTRY, DIP TYPE	
		APPLICATION SPEC		
		WEIGHT 4.95 GRAMS	SIZE A3	CAGE CODE 00779
MATERIAL SEE NOTE		FINISH SEE NOTE	DRAWING NO C=1734320	RESTRICTED TO
		CUSTOMER DRAWING	SCALE —	SHEET 1 OF 6
				REV B4

4


3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT 2011 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	APVD
				SEE SHEET 1.		



13 Kg	11 Kg	90	25	2250 PCS	3-1734320-X
14.4 Kg	12.4 Kg	100	25	2500 PCS	5-1734320-X 4-1734320-X 2-1734320-X 1-1734320-X 1734320-X
GROSS WEIGHT (Ref.)	NET WEIGHT (Ref.)	PCS/TRAY	TRAYS /BOX	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.2 3 PLC ±0.15 4 PLC ± ANGLES ±3°
MATERIAL	FINISH

DWN	CHK	APVD	PRODUCT SPEC	APPLICATION SPEC	WEIGHT

CUSTOMER DRAWING

TE TE Connectivity

NAME

MODULAR JACK CONNECTOR
RJ45, SINGLE PORT, SIDE ENTRY, DIP TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1734320	

SCALE — SHEET 6 OF 6 REV B4