



TABLE 1

YAZAKI SUB ASSEMBLY PART NO.	NO.	YAZAKI PART NO.	MATERIAL	COLOR	QTY.
△ 7282-7020-10 ETC.	①	SEE TABLE 2	PBT	SEE TABLE 2	1
	②	7157-4102	PBT	NATURAL	1

TABLE 2

YAZAKI SUB ASSEMBLY PART NO.	YAZAKI PART NO.	COLOR
△ 7282-7020	7182-7020	NATURAL
△ 7282-7020-10	7182-7020-10	DARK GRAY
△ 7282-7020-30	7182-7020-30	BLACK
△ 7282-7020-40	7182-7020-40	LIGHT GRAY
△ 7282-7020-50	7182-7020-50	ORANGE
△ 7282-7020-60	7182-7020-60	GREEN
△ 7282-7020-80	7182-7020-80	BROWN
△ 7282-7020-90	7182-7020-90	BLUE

注 記

1. 適用端子品番 : 7114-4025 ETC.
- △ 2. 適用ゴム栓品番 : 7158-3006-90 ETC.
- △ 3. 嵌合相手品番 : 7283-7020-10 ETC.

NOTES

1. APPLICABLE TERMINAL PARTS NO. : 7114-4025 ETC.
- △ 2. APPLICABLE RUBBER STOPPER NO. : 7158-3006-90 ETC.
- △ 3. MATING PART NO. : 7283-7020-10 ETC.

ISSUE MARK

△ 97.07.01	CHANGED FORM & ADDED PART NO.	C97-M145	H. K	CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	SEE TABLE 1	TREAT. & FIN.
△ 89.08.19	CHANGED FORM & RENEW	C89-L859	M. T	OFFICE	TRIAL PART NO.		NAME	090II 2P SEALED CONNECTOR	
89.02.22	NEW	C89-L377	T. M	VENDOR				HOUSING MALE SUB ASSEMBLY	
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR NO.		PART NO.	△ 7282-7020-10 ETC.	
GENERAL TOLERANCE				DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
A	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	R	NEW
B	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	88.12.08	mm/2/1
③	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED
③	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	CHECKED	DESIGN
SPECIFIED	MASS			g	加藤 山梨	高田 甲斐	M. TSUJI	DRAWN	ADYAMA
					97.07.04	97.07.03	97.07.03	88.07.27	97.07.01

YAZAKI CORPORATION