







|              |              |               |   |              |               |              |               |                      |                |            |           |             |
|--------------|--------------|---------------|---|--------------|---------------|--------------|---------------|----------------------|----------------|------------|-----------|-------------|
| 20.00(.7874) | 21.32(.839)  | 45.72(1.800)  | 1 | 0.102(.0040) | 40.13(1.580)  | 35.20(1.386) | 50.90(2.004)  | YES                  | POCKET TAPE    | YES        | 56        | 7-1658071-2 |
| 0(.000)      | 11.32(.446)  | 25.72(1.013)  | 0 | 0.102(.0040) | 20.13(.793)   | 15.20(.598)  | 30.90(1.217)  | YES                  | POCKET TAPE    | YES        | 28        | 7-1658071-1 |
| 20.00(.7874) | 21.32(.839)  | 45.72(1.800)  | 1 | 0.102(.0040) | 40.13(1.580)  | 35.20(1.386) | 50.90(2.004)  | YES                  | POCKET TAPE    | NO         | 80        | 6-1658071-2 |
| 0(.000)      | 11.32(.446)  | 25.72(1.013)  | 0 | 0.102(.0040) | 20.13(.793)   | 15.20(.598)  | 30.90(1.217)  | YES                  | POCKET TAPE    | NO         | 40        | 6-1658071-1 |
| 20.00(.7874) | -            | 45.72(1.800)  | 1 | 0.102(.0040) | 40.13(1.580)  | 35.20(1.386) | 50.90(2.004)  | NO                   | POCKET TAPE    | YES        | 56        | 5-1658071-2 |
| 0(.000)      | -            | 25.72(1.013)  | 0 | 0.102(.0040) | 20.13(.793)   | 15.20(.598)  | 30.90(1.217)  | NO                   | POCKET TAPE    | YES        | 28        | 5-1658071-1 |
| 20.00(.7874) | -            | 45.72(1.800)  | 1 | 0.102(.0040) | 40.13(1.580)  | 35.20(1.386) | 50.90(2.004)  | NO                   | POCKET TAPE    | NO         | 80        | 4-1658071-2 |
| 0(.000)      | -            | 25.72(1.013)  | 0 | 0.102(.0040) | 20.13(.793)   | 15.20(.598)  | 30.90(1.217)  | NO                   | POCKET TAPE    | NO         | 40        | 4-1658071-1 |
| 80.00(3.150) | 51.32(2.020) | 105.72(4.162) | 4 | 0.152(.0060) | 100.14(3.943) | 95.20(3.748) | 110.91(4.367) | YES                  | TRAY           | YES        | 140       | 3-1658071-5 |
| 60.00(2.362) | 41.32(1.627) | 85.72(3.375)  | 3 | 0.152(.0060) | 80.14(3.155)  | 75.20(2.961) | 90.91(3.579)  | YES                  | TRAY           | YES        | 112       | 3-1658071-4 |
| 40.00(1.575) | 31.32(1.233) | 65.72(2.587)  | 2 | 0.152(.0060) | 60.13(2.368)  | 55.20(2.173) | 70.90(2.791)  | YES                  | TRAY           | YES        | 84        | 3-1658071-3 |
| 20.00(.7874) | 21.32(.839)  | 45.72(1.800)  | 1 | 0.102(.0040) | 40.13(1.580)  | 35.20(1.386) | 50.90(2.004)  | YES                  | TRAY           | YES        | 56        | 3-1658071-2 |
| 0(.000)      | 11.32(.446)  | 25.72(1.013)  | 0 | 0.102(.0040) | 20.13(.793)   | 15.20(.598)  | 30.90(1.217)  | YES                  | TRAY           | YES        | 28        | 3-1658071-1 |
| 80.00(3.150) | 51.32(2.020) | 105.72(4.162) | 4 | 0.152(.0060) | 100.14(3.943) | 95.20(3.748) | 110.91(4.367) | YES                  | TRAY           | NO         | 200       | 2-1658071-5 |
| 60.00(2.362) | 41.32(1.627) | 85.72(3.375)  | 3 | 0.152(.0060) | 80.14(3.155)  | 75.20(2.961) | 90.91(3.579)  | YES                  | TRAY           | NO         | 160       | 2-1658071-4 |
| 40.00(1.575) | 31.32(1.233) | 65.72(2.587)  | 2 | 0.152(.0060) | 60.13(2.368)  | 55.20(2.173) | 70.90(2.791)  | YES                  | TRAY           | NO         | 120       | 2-1658071-3 |
| 20.00(.7874) | 21.32(.839)  | 45.72(1.800)  | 1 | 0.102(.0040) | 40.13(1.580)  | 35.20(1.386) | 50.90(2.004)  | YES                  | TRAY           | NO         | 80        | 2-1658071-2 |
| 0(.000)      | 11.32(.446)  | 25.72(1.013)  | 0 | 0.102(.0040) | 20.13(.793)   | 15.20(.598)  | 30.90(1.217)  | YES                  | TRAY           | NO         | 40        | 2-1658071-1 |
| 80.00(3.150) | -            | 105.72(4.162) | 4 | 0.152(.0060) | 100.14(3.943) | 95.20(3.748) | 110.91(4.367) | NO                   | TRAY           | YES        | 140       | 1-1658071-5 |
| 60.00(2.362) | -            | 85.72(3.375)  | 3 | 0.152(.0060) | 80.14(3.155)  | 75.20(2.961) | 90.91(3.579)  | NO                   | TRAY           | YES        | 112       | 1-1658071-4 |
| 40.00(1.575) | -            | 65.72(2.587)  | 2 | 0.152(.0060) | 60.13(2.368)  | 55.20(2.173) | 70.90(2.791)  | NO                   | TRAY           | YES        | 84        | 1-1658071-3 |
| 20.00(.7874) | -            | 45.72(1.800)  | 1 | 0.102(.0040) | 40.13(1.580)  | 35.20(1.386) | 50.90(2.004)  | NO                   | TRAY           | YES        | 56        | 1-1658071-2 |
| 0(.000)      | -            | 25.72(1.013)  | 0 | 0.102(.0040) | 20.13(.793)   | 15.20(.598)  | 30.90(1.217)  | NO                   | TRAY           | YES        | 28        | 1-1658071-1 |
| 80.00(3.150) | -            | 105.72(4.162) | 4 | 0.152(.0060) | 100.14(3.943) | 95.20(3.748) | 110.91(4.367) | NO                   | TRAY           | NO         | 200       | 1658071-5   |
| 60.00(2.362) | -            | 85.72(3.375)  | 3 | 0.152(.0060) | 80.14(3.155)  | 75.20(2.961) | 90.91(3.579)  | NO                   | TRAY           | NO         | 160       | 1658071-4   |
| 40.00(1.575) | -            | 65.72(2.587)  | 2 | 0.152(.0060) | 60.13(2.368)  | 55.20(2.173) | 70.90(2.791)  | NO                   | TRAY           | NO         | 120       | 1658071-3   |
| 20.00(.7874) | -            | 45.72(1.800)  | 1 | 0.102(.0040) | 40.13(1.580)  | 35.20(1.386) | 50.90(2.004)  | NO                   | TRAY           | NO         | 80        | 1658071-2   |
| 0(.000)      | -            | 25.72(1.013)  | 0 | 0.102(.0040) | 20.13(.793)   | 15.20(.598)  | 30.90(1.217)  | NO                   | TRAY           | NO         | 40        | 1658071-1   |
| H            | G            | F             | E | D            | C             | B            | A             | POLYIMIDE FILM PAD ▲ | PACKAGING TYPE | DIFF. PAIR | NO OF POS | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.  
DIMENSIONS: mm [INCHES]  
TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ± -  
1 PLC ± 0.3[.01]  
2 PLC ± 0.13[.005]  
3 PLC ± 0.05[1(.0020)]  
4 PLC ± -  
ANGLES ± 2°  
FINISH  
MATERIAL

DWN B. CARBO 26FEB03  
CHK D. DIXON 26FEB03  
APVD D. DIXON 26FEB03  
PRODUCT SPEC  
APPLICATION SPEC  
WEIGHT  
CUSTOMER DRAWING

TE Connectivity  
RECEPTACLE ASSEMBLY, VERTICAL,  
0.80MM CL,  
MICTOR SB  
SIZE A2 CAGE CODE 00779 DRAWING NO 1658071  
RESTRICTED TO  
SCALE 1:1 SHEET 2 of 2 REV L1