




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.27	阿树




E
D
C
B
A



CIRCUIT DIAGRAM

Code-x	H	Code-x	H
A	4.3	O	11.0
B	4.5	P	11.5
C	5.0	Q	12.0
D	5.5	R	12.5
E	6.0	S	13.0
F	6.5	T	13.5
G	7.0	U	14.0
H	7.5	V	14.5
I	8.0	W	15.0
J	8.5	X	15.5
K	9.0	Y	16.0
L	9.5	Z	17.0
M	10.0	18	18.0
N	10.5	19	19.0



PBC.WELDING DRAWING

The Main Thehnology Performance

Rate voltage current	50mA DC12V
Contact resistance	≤100mΩ
Operating force	±50gf
Tracel	0.25±0.10mm
Insulted resistance	≥100MΩ
Dielectric strength	≥250VAC/1min
life	≥300000 Cycles

E	Button	PPA	1	Black
D	Cover	SPCC	1	Copper-tinned plating
C	Shrapnel	SUS	1	Ag
B	Noumenon	PPA	1	Black
A	Cards	Brass	1	Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR

PAPT NO	TC-1102D-X-X-X
Operating Force	A:100gf B:160gf C:260gf
Height	Code-x
Color	B:Black

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	TACT SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	TC-1102D-X-X-X
APPROVED		SIZE:	A4	DWG NO.:	