


1

2

3

4



PANEL DETAILS







FIG 1
VLP-F
(FLAT)




FIG 2
VLP-D
(DOMED)

MATL: PC, RMS-23 CLEAR	FIGURE	"A"	"B"	"C"	"D"	"E"	"F"	"G"	"H"	PANEL THICKNESS
VLP1-F-1	1	12.7 [0.50]	4.7 [0.19]	1.50 [0.06]	3 [0.12]	6.4 [0.25]	2.5 [0.10]	4.7 [0.19]	1.5 ±0.05 [0.06 ±0.002]	0.8 [0.03] TO 3 [0.12]
VLP1-F-3		16.5 [0.65]								
VLP1-F-4		21.8 [0.86]								
VLP1-F-5		26.1 [1.03]								
VLP1-D-1	2	12.7 [0.50]								
VLP1-D-3		16.5 [0.65]								
VLP1-D-4		21.8 [0.86]								
VLP1-D-5		26.1 [1.03]								
VLP2-F-1	1	12.7 [0.50]	7.5 [0.30]	2.45 [0.10]	5 [0.20]	10 [0.39]	3 [0.12]	7.5 [0.30]	2.4 ±0.05 [0.09 ±0.002]	
VLP2-F-2		15 [0.59]								
VLP2-F-3		16.5 [0.65]								
VLP2-F-4		21.8 [0.86]								
VLP2-F-5		26.1 [1.03]								
VLP2-F-6		55 [2.17]								
VLP2-D-1	2	12.7 [0.50]								
VLP2-D-3		16.5 [0.65]								
VLP2-D-4		21.8 [0.86]								
VLP2-D-5		26.1 [1.03]								
VLP2-D-6		55 [2.17]								

ALTERNATE UNITS FOR REFERENCE ONLY

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

ALL DIMENSIONS IN mm
GENERAL TOLERANCES ±0.25
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°

THIRD ANGLE

MATERIAL:
POLYCARBONATE (RMS-23)

COLOUR:
CLEAR

DESCRIPTION:
VERTICAL LIGHT PIPE

PART No:
SEE TABLE

DRG No:
08-040

NPR No:
FR08-0031

SHEET SIZE
A4

DRN
MT

DATE
10/06/08

CHKD
TC

DATE
18/02/09

SCALE
NTS

SHEET No.
1 OF 1