

HUBER+SUHNER® DATA SHEET

Coaxial Cable Connector: 16_MMCX-50-2-1/111_O

Rev.: D



Description

Right angle cable plug

Interface Standards
SUHNER-MMCX

Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact soldered
Outer contact soldered
Weight 0.0006 kg

Environmental Data

Operating Temperature -55 °C to 155 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Hard Au min. 1.3 µm over Ni min. 1.3 µm
Outer contact	Brass	Hard Au min. 0.8 µm
Body	Brass	Hard Au min. 0.8 µm
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing DOU-00006007
Assembly instruction DOC-0000180777

Ordering Information

Single package 16_MMCX-50-2-1/111_OE
Bulk 100 pcs package 16_MMCX-50-2-1/111_OH

Additional Information

Suitable cable EZ_86_TP_M17

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG

RF Technology

9100 Herisau, Switzerland

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions