






技术要求:

1. 特性阻抗 50Ω
2. 频率范围 $0-6\text{GHz}$
3. 接触电阻 内导体 $\leq 3\text{m}\Omega$
外导体 $\leq 2\text{m}\Omega$
4. 绝缘电阻 $\geq 5000\text{M}\Omega$
5. 盐雾时间 24H
6. 分离力 $\geq 0.28\text{N}$
7. 温度范围 -55°C T_0 $+155^\circ\text{C}$



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: SMA 带孔 90° DIP L20.0
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW18-SMAW1300-2000B
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.
			DRAW NO: HYC-1905251328
			SHEET NO. 1 OF 1