





P.C.B. LAYOUT



CIRCUIT: SPST ▲

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 50mA @12VDC
- ▲ 5. OPERATING FORCE: 160± 50 gf
6. TRAVEL: 0.3mm ± 0.15mm
7. CONTACT RESISTANCE: 100 mΩ MAX.
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
- ▲ 9. CONTACT MATERIAL: GOLD
10. ▲ DENOTES CRITICAL PARAMETER
11. OPERATING TEMP: -40°C TO 85°C



D	24551	REMOVE STEP IN HOUSING, CHANGE TEMP	10/29/20	JM
C	19502	ADD TOLERANCE	12/08/10	BGL
B	16084	ADD GOLD DOME NOTE	6/5/06	CT
A	14996	RELEASED FOR PRODUCTION	6/15/05	JB
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE TL1105QF160R

SCALE 4:1

DATE 12/11/2009

DR JB

DWG P156000

REV D