




REV. B
DCO 300825


TOLERANCES $\pm .010"$ - UNLESS
OTHERWISE SPECIFIED

COIL: @ 25°C
RESISTANCE 400 OHMS $\pm 10\%$
NOMINAL VOLTAGE 28 VDC
MUST OPERATE 13.5 VDC MAX.
MUST RELEASE 5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:
VIBRATION 70 Hz TO 3000 Hz @ 30 g's
SHOCK 200 g's 6 MS. DURATION
TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE, RELEASE 6 MS MAX.
CONTACT STABILIZATION 2.5 MS MAX.
CONTACT BOUNCE 1 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL
5 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE
100,000 OPERATIONS

DR. B.D. 25APR2008 CK. 5/9/08 J.M.B.

Tyco Electronics ©COPYRIGHT 2005
TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CUST. M83536/5-020M
CUST. NO. ---- REV. ---
TE NUMBER 6-1617760-6

CII PART NUMBER
FCB-405-0520M