






PANEL THICKNESS	X dimension
0.75-1.25 [0.030-.049]	19.2-01 [7.56]
1.25-2.0 [0.049-.079]	19.4-01 [7.64]
2.0-3.0 [0.079-.118]	19.8-01 [7.80]



ACTUATOR:  BLACK POS. 1


 BLACK BODY/HOUSING



PANEL CUTOUT
NOT TO SCALE

SWITCH FUNCTION	
POS. 1	POS. 2
<ON>	OFF
1-1a	OPEN

() = MOMENTARY



CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4 X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR 8A @ 250VAC
5. MATERIALS: TERMINALS: Silver Plated Copper Alloy CONTACTS: Coin Silver, Silver Plated
6. ELECTRIC LIFE: 10,000 cycles
7. CONTACT RESISTANCE: <20 Mega Ω
8. INSULATION RESISTANCE: >1000 Mega Ω
9. DIELECTRIC STRENGTH: >1500 V 1 minute >3000 V between poles
10. 2002/95/EC (ROHS) COMPLIANT



TITLE			
A	17380	RELEASED FOR PRODUCTION	6/12/07 TN
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE		DATE	DR
1.5:1		6/12/07	TN
DWG		REV	A
M304198			