




GENERAL TOLERANCE										PART NO. AND CH. CODE	MATERIAL	COLOR		
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR				ANGLE	
A	±0.15	±0.2	±0.3	±0.5	±0.75								±3°	
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5				±3°	
Ⓒ	±0.3	±0.5	±0.8	±1.4	±2								±3°	
											2	PBT	NATURAL	
											2		7186-8851, A	GREEN
											2		7186-8851-60, A	BLACK
											3		7186-8851-30, A	BROWN
											3		7186-8851-80, A	BLUE
											4	7186-8851-90, A		

注記

1. かん合相手品番 : 7187-8856 ETC.
2. 適用端子品番 : 7114-7386-02 ETC.

NOTES

1. MATING PART NO. : 7187-8856 ETC.
2. APPLICABLE TERMINAL PART NO. : 7114-7386-02 ETC.



LET	DATE	REVISION RECORD		NO.	CHKD	GENERAL TOLERANCE					
		10MAX	50MAX			100MAX	250MAX	2500VR	ANGLE	ECCENT	
4	2016/02/04	ADDED PART NO.								C16-Z126	A.Q
3	2015/04/07	ADDED COLOR PART NO.								C15-Z136	A.Q
2	2014/09/16	ADDED COLOR NO. ETC.								C14-Z544	A.Q
1	2012/01/11	CHANGED FORM. <u>A</u>								C12-Z053	J.C
	2011/12/01	NEW								C11-Z971	J.C
SPECIFIED											
										MASS	