


LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			E	Contact pin base material change from CuSn (Phosphor bronze)to CuZn (Brass). Plating change from MIN. 0.8µm gold plating to min. 0.7µm Pd Ni + 0.1µm gold flash at contact area (Area F).	22JUL2014	TJ	JK

VERWENDET FÜR
E 88-52 549

POLZ. PRO REIHE	L±0.4	BESTELL-NR.
—	—	—
2	5.08	-2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	△3 ——— -6
7	17.78	△2 ——— -7
8	20.32	△2 ——— -8
9	22.86	△3 ——— -9
10	25.40	△2 1 ——— -0
11	27.94	△3 1 ——— -1
12	30.48	1 ——— -2
13	33.02	△1 1 ——— -3
14	35.56	△3 1 ——— -4
15	38.10	△2 1 ——— -5
16	40.64	1 ——— -6
17	43.18	1 ——— -7
18	45.72	△3 1 ——— -8
19	48.26	△3 1 ——— -9
20	50.80	2 ——— -0
21	53.34	△2 2 ——— -1
22	55.88	△3 2 ——— -2
23	58.42	2 ——— -3
24	60.96	△3 2 829192 -4
25	63.50	△2 2 ——— -5
26	66.04	△2 2 ——— -6
27	68.58	△3 2 ——— -7
28	71.12	2 ——— -8
29	73.66	△3 2 ——— -9
30	76.20	3 ——— -0
31	78.74	△3 3 ——— -1
32	81.28	△3 3 ——— -2
33	83.82	△3 3 ——— -3
34	86.36	△3 3 ——— -4
35	88.90	△3 3 ——— -5
36	91.44	△3 3 ——— -6
37	93.98	△3 3 ——— -7
38	96.52	△3 3 ——— -8
39	99.06	△3 3 ——— -9
40	101.60	4 ——— -0
41	104.14	△3 4 ——— -1
42	106.68	△3 4 ——— -2
43	109.22	△3 4 ——— -3
44	111.76	△3 4 ——— -4
45	114.30	△3 4 ——— -5
46	116.84	4 ——— -6
47	119.38	△3 4 ——— -7
48	121.92	△3 4 ——— -8
49	124.46	△3 4 ——— -9
50	127.00	△2 5 ——— -0

NICHT VERMASSTE KANTEN SIND NICHT MAßSTÄBLICH

- △1 STECKSEITE: IM BEREICH "F" 0.7µm PdNi+0.1µm GOLD FLASH
ÜBER 1.27µm NICKEL
- △2 LÖTSEITE: MIN. 2.5µm ZINN ÜBER 1.27µm NICKEL
- △2 OBSOLETE
- △3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



KONTAKTSTIFT	CuZn	△1
STIFTGEHÄUSE	PBT	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE
		FARBE

ZEICHNUNG GÜLTIG AB KW 26/90

DIMENSIONS: mm	DWN A.HO	28.09.88	MATERIAL	SEE TABLE	FINISH	SEE TABLE
	CHK M.SCHAARSCHMIDT	28.09.88				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD —	—				
0 PLC ±0.2 mm	PRODUCT SPEC	108-18012	NAME SPEZ. AMPMODU II STIFTELEISTE ZWEIREIHIG LOW COST LINE			
1 PLC ± —	APPLICATION SPEC	—				
2 PLC ± —	WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC ± —	CUSTOMER DRAWING		A4	00779	C-829192	—
4 PLC ± —			SCALE 4:1			
ANGLES ± —			SHEET	1 OF 1	REV	E

