






技术要求:

1. 特性阻抗 $50\ \Omega$
2. 频率范围 0-6GHz
3. 接触电阻 内导体 $\leq 3\text{m}\ \Omega$
外导体 $\leq 2\text{m}\ \Omega$
4. 绝缘电阻 $\geq 5000\text{M}\ \Omega$
5. 盐雾时间 24H
6. 分离力 $\geq 0.28\text{N}$
7. 温度范围 -55°C T0 $+155^\circ\text{C}$



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: SMA 180° DIP 偏脚带孔夹1.2 L13.5	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW21-SMAW0865-1350B	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱国夷	DATE : 2014-02-23	DRAW NO: HYC-2004081817	SHEET NO. 1 OF 1