



PART NO.	"A" REF	"B" REF FOR PART	"C"	"D"
FCCS-1	1.06 [27.0]	.59 [15.0]	.031 [0.80]	.13 [3.4]
FCCS-2	1.65 [42.0]	1.18 [30.0]	.039 [1.0]	.15 [3.7]
FCCS-3	1.85 [47.0]	1.38 [35.0]		
FCCS-4	2.24 [57.0]	1.77 [45.0]		
FCCS-5	2.83 [72.0]	2.36 [60.0]	.059 [1.50]	



NOTES:

1. MATERIAL: FLAME RETARDANT NYLON 6/6 (RMS-19)
NYLON 6/6 (RMS-01) AVAILABLE BY SPECIAL ORDER.
2. COLOR: NATURAL.
BLACK AVAILABLE BY SPECIAL ORDER.
TO ORDER USE PART NO. FCCS-XBK

TITLE: FLAT CABLE CLAMP, SNAP-IN				UNITS: INCH [mm]	
CREATED USING SOLIDWORKS	FILE #: FCCS	DWN: SK	APP: SK	FINAL	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1	SHEET SIZE: A	DT: 05/26/2005	CHKD: SJ	PART #
RE: RICHCO, INC.		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		SEE TABLE	
C	MADE "A" AND "B" PART DIMENSIONS REF, ECN # 1448	DZ	06/05/2019	PRINT TYPE CA	
B	ADDED COLOR BLACK, SEE CO 200697	SK	08/15/2011		
A	RELEASED FOR PRODUCTION	SK	06/09/2005		
REV.	DESCRIPTION	ENGR.	DATE		