




726ET SERIES MAGNETIC CIRCUIT




R1-R4 = 75 OHMS, 1/16W RESISTORS

C1 = 1000 pF, 2kV CAPACITOR



PIN DESIGNATIONS



SUGGESTED PCB LAYOUT
(Component Side)

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN L. VARELA - 15MAR2005 CHK D. FAROLE - D0CK5 15MAR2005		 trp CONNECTOR a bel group		DONGGUAN CHINA	
		APVD D. FAROLE 15MAR2005							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		MODEL NAME		DESC			
		0 PLC ± -		MAGJACK GANG		1X4 726ET 10/100 TAB UP W/ LED		-	
		1 PLC ± -							
		2 PLC ± .010							
		3 PLC ± .005							
4 PLC ± -		4 PLC ± -		NON-POE		SIZE A1		CAGE CODE	
PRODUCT SPEC 108-2100		APPLICATION SPEC -		CUSTOMER DRAWING		DRAWING NO C=6610023		RESTRICTED TO -	
						SCALE 4:1		SHEET 2 OF 2	
								REV G	