

## Coaxial Cable Connector 11\_SMA-50-2-65/119\_N

### Description

Straight cable plug

Interface standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	18 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0024 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	

### Related Documents

Outline drawing	DOU-00006097
Catalogue drawing	DOU-00006099
Assembly instruction	DOC-0000178687

### Ordering Information

Single package	11_SMA-50-2-65/119_NE
Bulk 100 pcs package	11_SMA-50-2-65/119_NH

### Additional Information

Suitable cables	EZ_86_TP_M17, SUCOFORM_86_FEP, MULTIFLEX_86
-----------------	---