




MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

SWITCH - TOGGLE
FLUSH KEY

CATALOG LISTING
2TP91 SERIES CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH


△4 CATALOG LISTING	CIRCUIT MADE WITH BUTTON DEPRESSED ON △3			ELECTRICAL DATA
	LUG SIDE (1-2, 4-5)	CENTER (1-2, 4-5)	OPPOSITE LUG (2-3, 5-6)	
	ON	OFF	ON	L191 15A 125, 250, 277 VAC 1/2HP 125 VAC 1HP 250, 277 VAC 5A 125 VAC "L" 
	OFF	NONE	ON	
	ON	NONE	ON	
	NONE	OFF	ON	
	NONE	ON	ON	
	MOM OFF	NONE	ON	L192 10A 125, 250, 277 VAC 1/4HP 125 VAC 1/2HP 250, 277 VAC 3A 125 VAC "L" 
	MOM ON	OFF	ON	
	MOM ON	NONE	OFF	
2TP91-7-	MOM ON	OFF	MOM ON	
	MOM ON	NONE	ON	
	NONE	ON	MOM ON	
	MOM ON	OFF	NONE	



BUTTON COLOR CODE △5	
COLOR IDENTIFICATION	COLOR
W	WHITE
R	RED
Y	YELLOW
BK	BLACK
G	GREEN
BL	BLUE
T	TRANSPARENT

- NOTES
- 1 - SWITCH WILL WITHSTAND TEMPERATURE OF 160°F
 - 2 - MICRO SWITCH CAT. LIST. MARKED ON SIDE OF SWITCH
 - △3 APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
 - △4 SUFFIX MUST BE ADDED FOR DESIRED BUTTON COLOR (EXAMPLE: 2TP91-1-BK)

ANSI Y14.5M-1982 APPLIES

THIRD ANGLE PROJECTION	
	
SCALE	FULL
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.0) ±.030
TWO PLACE	(.00) ±.015
THREE PLACE	(.000) ±.005
ANGLES	±
WEIGHT	.14 LB EST