




SUB ASSEMBLY PART NO.		PART NO.		MATERIAL		COLOR		QTY.	
AND CH. CODE		AND CH. CODE							
7282-8852-30, $\square/\Delta$		①		7182-8852-30		PBT		BLACK	
		②		Δ 7158-5263		PBT		Δ NATURAL	
								1	

NOTES

- MATING PART NO. : 7283-8852-30
- APPLICABLE TERMINAL NO. : 7114-4415-02 ETC.
- APPLICABLE SEAL RUBBER NO. : 7158-3165-90, 7158-3166-60, 7158-3167-80, 7158-3168-80
- APPLICABLE UNUSED CAVITY PLUG: 7158-3169-40

注記

- 嵌合相手品番 : 7283-8852-30
- 適用端子品番 : 7114-4415-02 ETC.
- 適用JIS検査品番 : 7158-3165-90, 7158-3166-60, 7158-3167-80
7158-3168-80
- 適用防水栓品番 : 7158-3169-40



③	03/08/07	CHANGED CODE, C	C03-X324	T. Y	CUSTOMER				MATL. SPEC.	SEE TABLE	TREAT. & F. IN.									
②	02/12/04	CHANGED FORM, B	C02-Y493	T. Y	CUSTOMER PART NO.				NAME	RH TYPE CONNECTOR 3P										
①	02/02/06	ELIMINATE SECTION, ETC.	C02-X199	T. Y																
	01/11/08	NEW	C01-Y135	T. Y	OFFICE	TRIAL PART NO.														
LET	DATE	REVISION RECORD		NO.	VENDOR	SUB ASSEMBLY MALE														
GENERAL TOLERANCE																				
	10MAX	50MAX	100MAX	250MAX	2500R	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.	7282-8852-30, C ③					
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	O. 1	R	NEW	01/11/08	mm	2/1	3	CH. CODE						
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	O. 1	APPROVED	CHECKED	CHECKED	DESIGN			DWG NO.	7282-8852-30:R	SET DRW NO.				
④	±0.3	±0.5	±0.8	±1.4	±2	±30°	O. 15													
SPECIFIED							MASS		8		03.08.19		03/08/19		01/05/08		03/08/07		YAZAKI CORPORATION	