


#### 技术说明

1.表明光洁，无明显缩坑与熔接痕

2. Current rating: 14A AC/DC

额定电流: 14A AC/DC

3.工作温度: -40°C - +125°C

K 282103 T M - B SN - X  
① ② ③ ④ ⑤ ⑥ ⑦

1.K: XKBTEK-Car Connector

2.XKB Series No

3.Category: T-Terminal

4.Special No: M-Male Terminal

5.Material: B-H65

6.Plating: SN-Plated Tin

7.Type: H-High foot ; L-Middle foot

M-Low feet

|                 |            |     |     |     |     |     |     |
|-----------------|------------|-----|-----|-----|-----|-----|-----|
| K282103TM-BSN-M | AWG#22-20  | 2.5 | 2.3 | 1.2 | 5.2 | 4.7 | 2.1 |
| K282103TM-BSN-L | AWG#18-15  | 3.2 | 3.3 | 1.2 | 5.2 | 4.7 | 2.1 |
| K282103TM-BSN-H | AWG#15-13  | 3.6 | 3.8 | 1.2 | 5.2 | 4.7 | 2.1 |
| PART NO         | Wire Range | U   | V   | W   | X   | Y   | Z   |

|                 |          |                     |                   |
|-----------------|----------|---------------------|-------------------|
| K282103TM-BSN-X | H65      | K282103HF           | K282103D          |
| PART NO         | Material | Suitable XKB Female | Suitable XKB Plug |

|      |  |             |                                           |
|------|--|-------------|-------------------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:<br>6.0mm Automobile connector |
| DWN  |  | VIEW:       | PART NO.:<br>K282103TM-BSN-X              |
| CHKD |  | UNIT: mm/in | DWG NO.:<br>X-K282103TM-BSN-X             |
| APPD |  | SIZE: A4    |                                           |

|                                               |  |  |  |  |                        |      |
|-----------------------------------------------|--|--|--|--|------------------------|------|
|                                               |  |  |  |  | ANGULAR                | ±5°  |
| ΔX                                            |  |  |  |  | L ≤ 4                  | ±0.2 |
| ΔX                                            |  |  |  |  | 4 < L ≤ 16             | ±0.3 |
| ΔX                                            |  |  |  |  | 16 < L ≤ 63            | ±0.4 |
| MARK                                          |  |  |  |  | L > 63                 | ±0.5 |
| REVISIONS                                     |  |  |  |  | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |  |  |  |  |                        |      |

**XKLB**

XKB INDUSTRIAL PRECISION CO., LIMITED

|        |       |          |
|--------|-------|----------|
| WEIGHT | SHEET | REVISION |
|        | 1/1   | A0       |