



MOUNTING RIVETS FOR THE FTH-28RS		
RIVET NO.	PANEL THICKNESS RANGE	MOUNTING HOLE DIA.
SR-3035	UP TO .034 (0.9)	.122-.126 (3.1-3.2)
SR-3045	.034-.073 (0.9-1.9)	
SR-3055	.073-.113 (1.9-2.9)	
SR-3065	.113-.152 (2.9-3.9)	
SR-3075	.152-.191 (3.9-4.9)	
SR-3080	.172-.211 (4.4-5.4)	
SR-3090	.211-.250 (5.4-6.4)	
SR-3100	.250-.290 (6.4-7.4)	

#4 (M3) SCREW TYPES FOR THE FTH-28RS
TRUSS, PAN, BINDING, OR ROUND HEAD

NOTES:

1. MATERIAL: NYLON 6/6, RMS-01.
2. COLOR: NATURAL.
3. TIE HOLDER TO ACCEPT EITHER A 3XXX SERIES RIVET OR A #4 (M3) SCREW.

D	SEE ECN #1124 FOR CHANGES	SK 01.24.06
C	UPDATED TABLE	RG 02.12.02
B	.33 WAS .316	RG 09.26.01
A	RELEASED FOR PRODUCTION	RG 09.26.01
REV	DESCRIPTION	ENGR DATE

TITLE: FLAT TIE HOLDER					DWG IN IN (MM)	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°		FILE # FTH-28RS	DWN: R.D.G.	APP:	FINAL	
MAT'L: SEE NOTES		DT: 05/16/01	DT:	PART #		PRINT TYPE
RE: RICHCO, INC.		RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		FTH-28RS-01		CA