


3

2

1

TABLE 1				TABLE 2			
SUB ASSEMBLY PART NO.		PART NO.		SUB ASSEMBLY PART NO.		PART NO.	
7283-1081 ETC.		①	△ SEE TABLE 2	7283-1081, △ (7C83-1081)		7183-1081 △(7B83-1081)	
		②	△ 7157-4108 (7B57-4108)	7283-1081-10, △		7183-1081-10, △	
		③	△ 7137-2215-30 (7B37-2215-30)	7283-1081-30, △ (7C83-1081-30)		7183-1081-30, △ (7B83-1081-30)	
				7283-1081-40, △		7183-1081-40, △	
				7283-1081-50, △		7183-1081-50, △	
				7283-1081-51, △		7183-1081-51, △	
				7283-1081-60, △		7183-1081-60, △	
				7283-1081-80, △		7183-1081-80, △	
				7283-1081-90, △		7183-1081-90, △	
						COLOR	
						NATURAL	
						DARK GRAY	
						BLACK	
						LIGHT GRAY	
						ORANGE	
						SAE ORANGE	
						GREEN	
						BROWN	
						BLUE	

B



△ SEC. A-A


注 記

- 1. 適用端子品番 : 7116-4025 ETC.
- 2. 嵌合相手品番 : 7282-1081 ETC.
- 3. 適用ゴム製品品番 : 7158-3006-90 ETC.
- 4. () 内品番は、エアバック回線及び特別管理回線に使用する時に適用する事。

NOTES

- 1. APPLICABLE TERMINAL NO. : 7116-4025 ETC.
- 2. MATING PART NO. : 7282-1081 ETC.
- 3. APPLICABLE RUBBER STOPPER NO. : 7158-3006-90 ETC.
- 4. () PART NO. IS USED FOR PARTS ASSOCIATED WITH A/B CIRCUITS OR OTHER SPECIFIED CIRCUIT.

A



A

△ 98.02.28	ADDED PART NO.	C98-L266	M. F
△ 97.05.27	CHANGED FORM & ADDED A/B PART NO. △	C97-L708	H. K
△ 96.10.04	CHANGED FORM & ADDED A/B PART NO. △	C96-M788	H. K
△ 94.05.27	CHANGED FORM	C94-L683	K. O
89.02.22	NEW	C89-L388	T. M
LET	DATE	REVISION RECORD	NO.
CHKD			
GENERAL TOLERANCE			
10MAX	50MAX	100MAX	2500VR
A ±0.15	±0.2	±0.3	±0.5
			±0.75
B ±0.2	±0.3	±0.55	±1.4
			±30'
C ±0.3	±0.5	±0.8	±2
			±30'
			0.15
SPECIFIED		MASS	
		g	