


7183-6097



△ 7183-6097-90

△ 7183-6097-40




7183-6152 (リブ違い品)

△ 7183-6152-60



24.70



注 記

- △ 1) かん合相手品番 : 7183-6152 : A (直結専用)
: 7183-6097 : A (直結専用)
: 7182-6097
- △ 2) 適用端子品番 : 7116-4780-02 (CAVS 0.3~0.5)
: 7116-4781-02 (CAVS 0.85~1.25)

NOTES

- △ 1) MATING PART NO. : 7183-6152 : A (DIRECT)
: 7183-6097 : A (DIRECT)
: 7182-6097
- △ 2) APPLICABLE TERMINAL NO. : 7116-4780-02 (CAVS 0.3~0.5)
: 7116-4781-02 (CAVS 0.85~1.25)



GENERAL TOLERANCE											
	10MAX	50MAX	100MAX	250MAX	250OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75					±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5	±3°	0.1
C	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15
						CUSTOMER		MATL. SPEC.		PBT	
						CUSTOMER PART NO.		CUSTOMER DWG NO.		TREAT. & FIN.	
						OFFICE		TRIAL PART NO.		NAME △ 060 6P HOUSING	
						VENDOR				FEMALE	
						VENDOR NO.					
						DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
						R	NEW	01.10.11	mm	2:1	3
						APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	
						S. MIZUSE		R. DE GUZMAN	S. KAYAMA	M. ALAGAR	
						10.11.15		10.11.15	00.10.26	10.11.15	
						PART NO. 7183-6097 ETC.					
						CH. CODE 7183-6097:R					
						DWG NO. 7183-6097:R					
						SET DWG NO.					
						YAZAKI CORPORATION					

GENERAL TOLERANCE					
	10MAX	50MAX	100MAX	250MAX	250OVR
A	±0.15	±0.2	±0.3	±0.5	±0.75
B	±0.2	±0.3	±0.55	±0.95	±1.4
C	±0.3	±0.5	±0.8	±1.4	±2
SPECIFIED					
MASS					