








RECOMMENDED P.C.B. LAYOUT




NOTES:

- ALL DIMENSIONS IN MM
- GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
- TERM. NOS. FOR REFERENCE ONLY.
- CONTACT RATING: 50mA @12VDC
- TRAVEL: $0.25 \pm 0.2/-0.1$ mm
- CONTACT RESISTANCE: 100mILLI-OHMS Max.
- OPERATING FORCE: 160 ± 50 gf
- CONTACT MATERIAL: SILVER
- ▲ DENOTES CRITICAL PARAMETER.
- ACTUATOR: TOP (6.15MM), BOTTOM (11.85)
- PACKAGE: TRAY/ 200 PIECES PER
- 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC



E-SWITCH®

TITLE TL53HCF160Q

B	19576	DRAWING UPDATE / CLEAN-UP	1/11/11	BGL
A	17000	RELEASED FOR PRODUCTION	2/20/07	TN

REV	PCR NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				

SCALE	2:1	DATE	2/20/2007	DR	TN	DWG	P010686	REV	B
-------	-----	------	-----------	----	----	-----	---------	-----	---