


SIGN	DATE	DESCRIPTION	APPROVER
△	9/17'10	How to order is changed	Runner
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	



Material:

- Item ① Terminal(housing): PA66 30% GF (UL94V-0)
- Item ② Contact pin of short: copper.tin plated

Electrical:

- Voltage rating: 160V
- Current rating: 5.5A
- Withstanding Voltage: 1.32 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ±10°C/5 Sec
- APPROVAL: 

cULus

KE xx 1 1 x 0 xxxx G

No. OF POLES

04: 2×2 POLES

06: 2×3 POLES

:

48: 2×24 POLES

COLOR

0 Black (RAL9005)

2 Red (RAL3001/D)

3 Orange(RAL2011/P)

4 Yellow(RAL1018/A)

5 Green(RAL6018/T)

6 Blue (RAL5015/A)

8 Grey(RAL7035/D)

G: Pb<40000ppm

A00 0: "@" Mark

△ A00 A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

POLE		2x2	2x3	2x4	2x5	2x6	2x7	2x8	2x9	2x10	2x11	2x12
A		8.50	12.00	15.50	19.00	22.50	26.00	29.50	33.00	36.50	40.00	43.50
B		3.50	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50
Tol.		±0.15					±0.20					
POLE	2x13	2x14	2x15	2x16	2x17	2x18	2x19	2x20	2x21	2x22	2x23	2x24
A	47.00	50.50	54.00	57.50	61.00	64.50	68.00	71.50	75.00	78.50	82.00	85.50
B	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50
Tol.		±0.25					±0.30					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KE 3.5mm W/O Flange Series (Vertical) DIP type											
PART NO.	KExx11x0xxxxG						DWG NO.	8KE0010				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance				
		Runner 2010.09.17	Runner 2010.04.12		UNIT: mm			X.	±0.50			
					SCALE: NONE			X.X	±0.30			
					SHEET: 01/01			X.XX	±0.10			
					REV.: C			X°	±1°			