






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. A14839	03MAY1995	JN	RDR
	A	REDESIGNED AND REDRAWN PER E.O. P15113	04OCT1996	JN	RDR
	B	REVISED PER PCN E-18-012207	31JUL2018	JA	DM
	B1	REVISED PER PCN E-19-004586	21MAR2019	JA	DM

2. WIRE RANGE: 20 AWG TO 16 AWG [0.5 - 1.5 mm²].
1. RECOMMENDED CRIMP TOOL: DEUTSCH HDT-48-00.

NOTES: UNLESS OTHERWISE SPECIFIED

TE INTERNAL PN	DEUTSCH PN	PLATING
0462-221-16141	0462-221-16141	NICKEL
0462-221-1631	0462-221-1631	GOLD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. NORRIS	02OCT1996		 TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK -	-		NAME SOCKET CONTACT EXTENSION BODY SIZE 16, 16-18 AWG DT SERIES		
		APVD R. REED	04OCT1996				
		PRODUCT SPEC 108-151004					
		APPLICATION SPEC 114-151004		SIZE A3	CAGE CODE 4AFU8	DRAWING NO C-0462-221-16XX	RESTRICTED TO -
		WEIGHT 1.49g		SCALE 7:1			
		CUSTOMER DRAWING					
MATERIAL		FINISH		SHEET 1 OF 1		REV B1	