






YAZAKI SUB ASS'Y PART NO.	NO.	YAZAKI PART NO.	MATERIAL	COLOR	QTY.
7282-3020 ETC.	①	SEE TABLE 2	△ HPA	SEE TABLE 2	1
	②	7157-4338	△ HPA	△ NATURAL	1

TABLE 2	YAZAKI SUB ASS'Y PART NO.		YAZAKI PART NO.	COLOR
		7282-3020, □	7182-3020	NATURAL
		7282-3020-10, □	7182-3020-10	DARK GRAY
		7282-3020-30, □	7182-3020-30	BLACK
		7282-3020-40, □	7182-3020-40	LIGHT GRAY
		7282-3020-50, □	7182-3020-50	ORANGE
		7282-3020-60, □	7182-3020-60	GREEN
		7282-3020-80, □	7182-3020-80	BROWN
		7282-3020-90, □	7182-3020-90	BLUE

△	
△	

品
共

1. 接合相手品番 : 7283-3020 ETC.
-
2. 適用端子品番 : 7114-6041 ETC.

NOTES

- 1.MATING PART NO. : 7283-3020 ETC.
-
- 2.APPLICABLE TERMINAL PART NO. : 7114-6041 ETC.

A		95.12.19	CH. FORM, MATERIAL & ADD. PART NO., ☒		C95-N071	H. K										
		89.07.19	NEW		C89-L352	H. I										
LET		DATE	REVISION RECORD		NO.	C-KD										
GENERAL TOLERANCE																
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT									
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1									
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1									
C	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15									
SPECIFIED								MASS					g			
CUSTOMER																
CUSTOMER PART NO.					CUSTOMER DWG NO.											
OFFICE					TRIAL PART NO.											
VENDOR					VENDOR NO.											
MATERIAL SPEC.		SEE TABLE 1			TREAT. & FIN.											
NAME		312 2P CONNECTOR			SUB ASS'Y MALE											
PART NO.		7282-3020 ETC.														
CH. CODE		7282-3020: R														
DWG NO.		Y. SAWADA SATOH														
YAZAKI CORPORATION		96.01.10			96.01.09			96.01.08			88.10.03			95.12.19		