





技术要求:

- 特性阻抗 50Ω
- 频率范围 0-6GHz
- 接触电阻 内导体 $\leq 3m \Omega$
外导体 $\leq 2m \Omega$
- 绝缘电阻 $\geq 5000M \Omega$
- 盐雾时间 24H
- 分离力 $\geq 0.28N$
- 温度范围 $-55^{\circ}C$ TO $+155^{\circ}C$

公差Tolerance	± 0.05	± 0.1	± 0.2	± 0.3	± 0.5	± 0.05	$\pm 0.5^{\circ}$
尺寸范围	0-10	10-20	20-50	50-100	>100	D<20	0-180°
Dimension	线型/Linear					孔Hole	角度Angle
Range	未注尺寸公差/Tolerance unless specified						



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2^{\circ}$ X.X' $\pm 0.5^{\circ}$ UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: SMA 带孔90° DIP L14.5	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW09-SMAW1300-1450B
	APPROVED BY:	DATE : 2014-02-23	MOLD NO.	
	邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2212011529
			SHEET NO.	1 OF 1