



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ECR-19-013004	26AUG2019	SR	JL
	B2	ECR-20-000836	23JAN2020	SB	JL
	B3	ECR-20-002949	02MAR2020	SR	JL
	B4	ECR-20-006986	18MAY2020	SR	DD

- 1 MATERIALS:
HOLDER: PBT ,COLOR: NATURAL;
CONTACTS: COPPER ALLOY, Au/Ni PLATING (LED INTERFACE)
2. FOR SOLID, FUSED AND STRANDED CONDUCTOR WIRE TYPES AWG 18 AND 20
3. WIRE STRIP LENGTH: 11-12mm
4. MAX. WIRE INSULATION OUTER DIA: Ø2,3mm
5. RECOMMENDED SCREW TORQUE: SEE APPLICATION SPECIFICATION 114-133107.
6. SCREWS TO BE USED: M3, #4-40
7. LED MATING ON 2 CORNERS WITH ADHESIVE TAPE 3M 9472LE 300LSE.
- 8 LAYOUTS ON SHEET 4
9. FOR COB-TO-HOLDER CROSS REFERENCE,
REFER TO APPLICATION SPECIFICATION 114-32208
- 10 PACKAGED ONE TRAY OF 20 PCS PER BOX, 10 BOXES PER SHIPPING CARTON.



PAN HEAD
SCALE 3:1



COUNTERSINK
SCALE 3:1

10	B	COUNTERSINK	5-2325807-3
	B	PAN HEAD	4-2325807-3
	A	PAN HEAD	4-2325807-2
	B	COUNTERSINK	1-2325807-3
	B	PAN HEAD	2325807-3
	A	COUNTERSINK	1-2325807-2
	A	PAN HEAD	2325807-2
	LED LAYOUT 8		DESCRIPTION
			PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 18DEC2017	 TE Connectivity			
		CHK J. LATORRE 18DEC2017				
DIMENSIONS:		APVD -	NAME			
mm		PRODUCT SPEC	LED HOLDER, 19x19			
		108-133062	LUMAWISE Z45 LED			
		APPLICATION SPEC	-			
		114-133107	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL		WEIGHT	A2	00779	C-2325807	-
1		CUSTOMER DRAWING	SCALE	2:1	SHEET	1 OF 4
					REV	B4

D

D

C


C


B

B


A

A





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 18DEC2017	 TE Connectivity					
		CHK J. LATORRE 18DEC2017						
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME LED HOLDER, 19x19 LUMAWISE Z45 LED -					
mm		PRODUCT SPEC 108-133062						
	0 PLC ± 1 PLC ±0.2 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±2°	APPLICATION SPEC 114-133107	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
	MATERIAL	FINISH - -	WEIGHT -	A200779	C-2325807	-		
CUSTOMER DRAWING			SCALE	3:1	SHEET	2 OF 4	REV	B4


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SECTION Y - Y
4-2325807-2 SHOWN



SECTION V - V
4-2325807-3 SHOWN



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 18DEC2017		 TE Connectivity					
		CHK J. LATORRE 18DEC2017							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME LED HOLDER, 19x19 LUMAWISE Z45 LED -					
		APVD -							
		PRODUCT SPEC 108-133062							
		APPLICATION SPEC 114-133107							
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
				A2	00779	C-2325807	-		
CUSTOMER DRAWING				SCALE	2:1	SHEET	3 of 4	REV	B4

D

D

C

C


B

B


A

A

LED SUBSTRATE LAYOUT A
TOP SIDE OF BOARD



LED SUBSTRATE LAYOUT B
TOP SIDE OF BOARD



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C. DAILY
CHK
J. LATORRE
APVD
-

18DEC2017
18DEC2017

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0.2
2 PLC	±0.13
3 PLC	±-
4 PLC	±-
ANGLES	±2°
FINISH	-
	-

PRODUCT SPEC
108-133062
APPLICATION SPEC
114-133107
WEIGHT
-

CUSTOMER DRAWING

SCALE
2:1

SHEET
4 OF 4

REV
B4

NAME
LED HOLDER, 19x19
LUMAWISE Z45 LED
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2325807

RESTRICTED TO
-

TE Connectivity