




GENERAL TOLERANCE											
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4					±3°	0.1
C	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15



PART NO. AND CH. CODE	MATERIAL	COLOR
7182-8049, [A]	PBT	NATURAL
7182-8049-30, [A]		BLACK

注記

- 適用端子品番 : 7114-4100-02 ETC.
- かん合相手品番 : 7183-8049 ETC.
- クリップ仕様 ・ パネル穴 : $\phi 7.2_{\pm 0.1} \times 10.2_{\pm 0.1}$ (長円)
・ 板厚 : $t = 0.6 \sim 2.0$

NOTES

- APPLICABLE TERMINAL PART NO. : 7114-4100-02 ETC.
- MATING PART NO. : 7183-8049 ETC.
- SPECS OF CLIP ・ PANEL HOLE : $7.2_{\pm 0.1} \times 10.2_{\pm 0.1}$ (SLOT)
・ PANEL THICKNESS : $t = 0.6 \sim 2.0$

4	10/10/15	CHANGED PART NAME	C10-ZA77	J. G
3	05/06/23	ADDED COLOR PART NO., ETC.	C05-Z973	M. K
2	04/11/08	CHANGED FORM, [A]	C04-ZA91	M. M
1	03/05/16	CHANGED NOTES	C03-X333	M. M
	02/09/16	NEW	C02-Y026	K. Y
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15
SPECIFIED						MASS	

CUSTOMER										MATL. SPEC.		TREAT. & FIN.		ISSUE MARK	
CUSTOMER PART NO.					CUSTOMER DWG NO.					③ SEE TABLE					
OFFICE					TRIAL PART NO.					NAME		④ 060 2P HOUSING MALE			
VENDOR															
VENDOR NO.															
DWG TYPE		DWG SOURCE			DWG DATE		UNIT	SCL	ANGLE	PART NO.		③ 7182-8049 ETC.			
R		NEW			02/09/16		mm	2:1	3	CH. CODE					
APPROVED		CHECKED		CHECKED		DESIGN		DRAWN		DWG NO.		7182-8049:R		SET DWG NO.	
S. MIZUSE		_____		R. DE GUZMAN		K. YOSHIDA		J. GAMBOA							
10/10/15		_____		10/10/15		02/01/25		10/10/15				YAZAKI CORPORATION			