


SAI-M23-SE-7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Pinning**

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Version	Sensor/Actuator plug-in connector, Insert
Order No.	1170030000
Type	SAI-M23-SE-7
GTIN (EAN)	4032248962143
Qty.	1 pc(s).

SAI-M23-SE-7

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	2 g
------------	-----

Technical data customisable plug-in connectors

Coding	none	Coding possibilities for M23 signal inserts	H, N, S, X, Y
Housing main material	Thermoplastic polyamide PA 6, PBT	Number of poles	7
Plugging cycles	> 1000	Pollution severity	3
Rated current	20 A	Rated current	2 mm contact= 20 A
Rated voltage	300 V	Rated voltage	2 mm contact= 300 V
Type of connection	Crimp connection		

Classifications

ETIM 6.0	EC000438	ETIM 7.0	EC003557
ETIM 8.0	EC003557	ECLASS 9.1	27-44-02-05
ECLASS 10.0	27-44-02-23	ECLASS 11.0	27-44-02-23
ECLASS 12.0	27-44-02-23		

Important note

Product information	Enclosures, inserts and crimp contacts need to be ordered separately.
---------------------	---

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN


SAI-M23-SE-7

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Pinning



Dimensioned drawing



Technical data

Technical data									
Number of positions	6	7	9		12	16	17	19	
Number of contacts	6	7	8	1	12	16	17	16	3
Contact Ø	mm	2	2	1	2	1	1	1	1.5

