




MATERIAL 材料:

HOUSING 外壳: PA10T,UL94V-0,BLACK.

TERMINAL 端子: PHOSPHOR BRONZE T=0.35MM, GOLD PLATING

SHIELD 保护物: NICKEL 50U" PLATED ON ALL AREA.

MECHANICAL 机械:

DURABILITY 耐用性: 750 CYCLES MIN,12.5MM/MINUTE.

INSERTION FORCE 插入力:2.2KG.F MAX

RETENTION STRENGTH 保持力:7.7KG.F BETWEEN JACK AND PLUG.

OPERATING TEMPERATURE 工作温度: -40°C~+85°C.

STORAGE TEMPERATURE 储存温度: -40°C~+85°C.

ALL CRITICAL DIMENSIONS WITH ""

ELECTRICAL 电气:

VOLTAGE 电压: 125 VOLTS AC.

CURRENT RATING 电流额定值: 1.5AMP.

DIELECTRIC STRENGTH 介电强度: 1000 VAC RMS 50HZ OR 60HZ,1 MIN


INSULATION RESISTANCE 绝缘电阻: 500 MEGA OHMS MIN.INITIAL

AFTER 500V DC FOR 1 MINUTE.

CONTACT RESISTANCE 接触电阻:SINGLE TERMINAL 30 MILLIOHMS MAX.

INITIAL 50 MILLIOHMS MAX. AFTER

DURABILITY TEST.





LED Specification

Standard	LED Color	LED Wavelength	Foward(A)	Foward(V)
	Green	568nm	20mA	1.8-2.8V
	Yellow	585nm	20mA	1.8-2.8V

X47ADAB1W9DB1157

1:AU=1U"
3:AU=3U"
4:AU=6U"
5:AU=15U"
6:AU=30U"



							DSND		SCALE: N/A	MODEL TYPE: RJ JACK			
ΔX					ANGLAR	±5°		DWN		VIEW: 	PART NO.:		
ΔX					L≤ 4	±0.2		CHKD		UNIT: mm/in	DWG NO.:		
ΔX					4<L≤ 16	±0.3					X47ADAB1W9DB1157		
ΔX					16<L≤ 63	±0.4		APPD		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED	L> 63						
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn													
											WEIGHT	SHEET	REVISION
												1/1	A0