



REV	ECN	APP'D
-	5484	JT 6/28/04



- NOTES:
1. CONFORMS TO PERFORMANCE REQUIREMENTS OF MIL-PRF-12883.
 2. MATERIALS:
 - A. HOUSING - POLYETHERIMIDE, COLOR: BLUE-GREEN.
 - B. GROMMET - SILICONE ELASTOMER, 50±10 DUROMETER, COLOR: RED.
 3. SOCKET CONTACTS CONFORM TO PERFORMANCE REQUIREMENTS OF MIL-C-39029, GOLD OVER NICKEL PLATE - SEE TABLE.
 4. COMPLETE MOUNTING HARDWARE SUPPLIED.
 5. OPERATING TEMPERATURE: +125°C/-65°C CONTINUOUS.
 6. CONTACT INSTALLATION TOOLS:

CRIMP TOOL: M22520/1-01
POSITIONER: M22520/1-02
INSERTION/REMOVAL: M81969/14-03.

PART NO.	CONTACTS SUPPLIED	MARKING
RSE116682	NONE	RSE116683
RSE116683	(14) SIZE 16/16, M39029/92-533	

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd SPECIFICATION DRAWING		TITLE RELAY SOCKET, 16 POS, SIZE 16, M12883/40-24			
ANSI Y14.5M UNITS: INCHES ACAD FILE	.XX ±.01 .XXX ±.005 ANGLES ±2°		ENGR S. KONDO 6/25/2004					
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC. PEABODY, MA	CHKD R. NEWMAN 6/28/04		SIZE B	DWG NO. RSE116682		REV —	
		APPD J. TON 6/28/04		CODE: 58982		SCALE: 3:2	SHEET 1 OF 1	