

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.	

NOTES

PHYSICAL PROPERTIES:

HOUSING MATERIAL: PBT

FLAMMABILITY: UL94V-0

COLOR: BLACK

MAX BOW/WARP: .0056 IN/IN.

TERMINAL:

TERMINALS: BRASS, TIN PLATED. (UNLESS OTHERWISE STATED)

SCREWS: 8-32 STEEL, NICKEL PLATED. (UNLESS OTHERWISE STATED)

Q.C. TABS: BRASS, NICKEL PLATED.

MECHANICAL:

PITCH (TERMINAL SPACING): .563"

WIRE RANGE: 10-22 AWG

RECOMMENDED TIGHTENING TORQUE: 14IN-LBS MAX.

ELECTRICAL PROPERTIES:



MAXIMUM CURRENT: 30A

OPERATING VOLTAGE: 600V

ENVIRONMENTAL PROPERTIES:

OPERATING TEMP RANGE: -40° TO +120°C

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
	B	PANEL MOUNTING HOLES CHANGED	23JUN16	FP



-	-	-	-	-	-	-	-	-	10.701	11.138	18	1-1986158-8
-	-	-	-	-	-	-	-	-	10.138	10.575	17	1-1986158-7
-	-	-	-	-	-	-	-	-	9.575	10.012	16	1-1986158-6
-	-	-	-	-	-	-	-	-	9.012	9.449	15	1-1986158-5
-	-	-	-	-	-	-	-	-	8.449	8.886	14	1-1986158-4
-	-	-	-	-	-	-	-	-	7.886	8.323	13	1-1986158-3
-	-	-	-	-	-	-	-	-	7.323	7.760	12	1-1986158-2
-	-	-	-	-	-	-	-	-	6.760	7.179	11	1-1986158-1
-	-	-	-	-	-	-	-	-	6.197	6.634	10	1-1986158-0
-	-	-	-	-	-	-	-	-	5.634	6.071	9	1986158-9
-	-	-	-	-	-	-	-	-	5.071	5.508	8	1986158-8
-	-	-	-	-	-	-	-	-	4.508	4.945	7	1986158-7
-	-	-	-	-	-	-	-	-	3.945	4.382	6	1986158-6
-	-	-	-	-	-	-	-	-	3.382	3.819	5	1986158-5
-	-	-	-	-	-	-	-	-	2.819	3.256	4	1986158-4
-	-	-	-	-	-	-	-	-	2.256	2.693	3	1986158-3
-	-	-	-	-	-	-	-	-	1.693	2.130	2	1986158-2
NOTES	8 .250 QC TAB 90° DOUBLE SIDE	7 .250 QC TAB 90°/45° DOUBLE SIDE	6 .250 QC TAB 90° DOUBLE SIDE	5 .250 QC TAB 45° DOUBLE SIDE	4 .250 QC TAB STRAIGHT DOUBLE SIDE	3 .250 QC TAB 90° SINGLE SIDE	2 .250 QC TAB 45° SINGLE SIDE	1 .250 QC TAB STRAIGHT SINGLE SIDE	DIM B	DIM A	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN
S SCHLEGEL
3/6/07

CHK
S YODER
3/6/07

APVD
S YODER
3/6/07

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
0.000000

CUSTOMER DRAWING

TE Connectivity

NAME
14.3 (.563) DBL ROW BARRIER STRIP
WASHER, 600v
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1986158

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 1

REV
B