







FRONT VIEW



BOTTOM VIEW




RIGHT SIDE VIEW

RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE

X12ADJB1A1DY1

1:AU=1U"
3:AU=3U"
4:AU=6U"
5:AU=15U"
6:AU=30U"



MATERIAL 材料:

HOUSING 外壳: PBT,UL94V-0,BLACK.

TERMINAL 端子: PHOSPHOR BRONZE Ø=0.46MM,GOLD PLATING

MECHANICAL 机械:

DURABILITY 耐用性: 750 CYCLES MIN,12.5MM/MINUTE.

INSERTION FORCE 插入力:2.2KG.F MAX

RETENTION STRENGTH 保持力:7.7KG.F BETWEEN JACK AND PLUG.

OPERATING TEMPERATURE 工作温度: -40°C~+85°C.

STORAGE TEMPERATURE 储存温度: -40°C~+85°C.

ALL CRITICAL DIMENSIONS WITH "***"

ELECTRICAL 电气:

VOLTAGE 电压: 125 VOLTS AC.

CURRENT RATING 电流额定值: 1.5AMP.

DIELECTRIC STRENGTH 介电强度: 1000 VAC RMS 50HZ OR 60HZ,1 MIN

INSULATION RESISTANCE 绝缘电阻: 500 MEGA OHMS MIN.INITIAL



AFTER 500V DC FOR 1 MINUTE.

CONTACT RESISTANCE 接触电阻:SINGLE TERMINAL 30 MILLIOHMS MAX.

INITIAL 50 MILLIOHMS MAX. AFTER
DURABILITY TEST.

LED Specification

Standard	LED Color	LED Wavelength	Foward(A)	Foward(V)
	Green	568nm	20mA	1.8-2.8V
	Yellow	585nm	20mA	1.8-2.8V



						DSND	SCALE: N/A	MODEL TYPE: RJ JACK		
ΔX					ANGLAR	±5°	DWN	VIEW:	PART NO.:	
ΔX					4<L≤ 16	±0.3	CHKD	UNIT: mm/in	DWG NO.:	
ΔX					16<L≤ 63	±0.4	APPD	SIZE: A4	X12ADJB1A1DY1	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5				WEIGHT
REVISIONS						UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO.,LIMITED			SHEET
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn										REVISION
										1/1
										A0